



CerPrint 3500/3710 Unfluxed Decal Donor Paper

Lamination Method, Decal Donor Paper for Your
CerPrint 3500/3710 Ceramic Decal Printer

- PACK OF 50 sheets of unfluxed donor paper.
- For use with the lamination process only. Do not use the donor paper directly in the CerPrint 3500/3710. *Print on shiny side of white waterslide paper only.*
- Does not contain flux, for in-glaze methods.
- Requires a laminator, see user manual.
- Fires from up to 2200°F



Firing Schedule

(see user manual)

Rate 1 50F/Hr to 160F

Hold 30 minutes

Rate 2 250F/hr to 850F

Rate 3 400F/hr to 2000F

Hold 30 minutes.

To order, call:

(800) 937-4224, Opt. 1

Or

Email: orders@rosettatechnologies.com

Part Number - 11930009