



Product Configuration



Space Requirements and Planning Guide



Plan ahead and make sure your installation is a great success! Remember to check the latest information on these products and make sure that the following items are available prior to installation.

- Verify power dedication and check for power stability. The MX-C250/MX-C300W Document Communication System requires AC 120V, 60Hz, 9 Amps power source.
- Confirm that you have the latest firmware available to upgrade the MX-C250/MX-C300W Document Communication System immediately.
- Make sure the customer has enough supplies on-hand to do a large rush job. After-hours printing and/or holiday work may take place immediately following an installation.

MX-C30NTB	Black Toner Cartridge
MX-C30NTC	Cyan Toner Cartridge
MX-C30NTM	Magenta Toner Cartridge
MX-C30NTY	Yellow Toner Cartridge

- Check to see if My Sharp™ online training is set up for the end-user.

Approximate Dimensions with Tray and Cover Open.

